

# Pulsation Damper Bladderless No Moving Parts Dissipative Dispersive

## WAG/Cer-RJ

## WAVEGUARD


Bladder-less, Foam-less, No Moving parts, Combo Damper.



Licensed M. Packer  
Since 1963

PULSATION DE-COUPLER - INTERCEPTOR - DISSIPATOR - DISPERSER

Fit and forget - service free DAMPERS



Over All Length „OAL“ =  
Vessel Length =  
Outside Diameter „OD“ =



Item	Part No.	Description	Material	I.D. #	Contact :
1		Inlet, 2:1 Semi-Elipsoidal Forged Head	Edelstahl DIN 1.4404		CUSTOMER:
2		Outlet, 2:1 Semi-Elipsoidal Forged Head	Edelstahl DIN 1.4404		CUSTOMER REF.:
3		Body Pipe Shell	Edelstahl DIN 1.4404		QUANTITY:
4		Explosive Decompression Dissipation Cage	Edelstahl DIN 1.4404		W/O No.:
5		RamJet Acceleration Wave Compression „Snokel“	Edelstahl DIN 1.4404		W: 100% GTAW 309ss
6		NPT or 37,5° Weld Bevel connections	Edelstahl DIN 1.4404		WEIGHT (EST.):
7		Flush-out point plug (for particulate systems)	Edelstahl DIN 1.4404		ISSUED BY:
8		Mirriad lengths conduit, frequency spectrum generator for amplitude reduction by dispersion	Keramik „Ballatini“		CHECKED BY:
					ISSUE DATE: (DAY/MONTH/YEAR)

**PulseGuard** <http://www.PulseGuard.com>  
**PulseGuard für Deutschland** <http://www.PulseGuard.co.uk>  
**PulseGuard, de langue Française** [www.pulsationdaempfer.com](http://www.pulsationdaempfer.com)  
**PulseGuard, de langue Francaise** [www.pulsationdaempfer.com](http://www.pulsationdaempfer.com)  
**PulseGuard, en Espagnol / and Américain** [www.pulsationdaempfer.com](http://www.pulsationdaempfer.com)  
**PulseGuard, diya Russkogovoryaschih** [www.pulsationdaempfer.com](http://www.pulsationdaempfer.com)  
 PulseGuard is the USA registered trade mark of PulseGuard Inc.  
 PulseGuard is the UK registered trade mark of PulseGuard Ltd.  
 UK --44(0)161-480-9625 USA --1910-270-2737  
**PulsationsDämpfer**  
ISO 9001 - 95:2004-40-451 Vessel Cert. 28219  
[www.pulseguard.co.uk](http://www.pulseguard.co.uk)  
 In association with ShockGuard Ltd & Liquid Dynamics International Ltd

TITLE: **Der Kombination Typ „zerstreuen“+„verbrauchen“**

APPLICATION:  
**Druck Pulsationsdämpfer ohne bewegliche Teile !!  
 Prevent System Response Pulsations  
 from Amplifying and Resonating with  
 the Forcing Action.**

SCALE: NTS ALL DIMENSIONS ARE IN MM EXCEPT AS STATED.

Artikel Nr.  
Wag-Cer-RJ-De

SHEET: 1 OF 1 REV. 0